








TDS PRODUCT IMAGE SHEET – CATEGORY > **GEARS, SPRINGS & CABLES**

Image	TDS Part Number & Description	OE & Alternative Part References (WHERE FITTED)
	<p>ASY201T SLIDE CLUTCH 100mm PURPLE SPRING (INST-046-06)</p> <p># SLIDE CLUTCH ARM ASSY +PIN = ASY200T-02 # CLUTCH PIN ONLY = PP004-CH</p>	<p>ASY201T TDS TREKA BUS 16/MELLOR MAXIMA+STRATA HF</p>
	<p>ASY202T SLIDE CLUTCH 100mm BLACK SPRING (INST-014-07)</p> <p># CLUTCH PIN ONLY = PP004-CH</p>	<p>ASY202T TDS PARRY PPM60</p>
	<p>GER001A SPUR GEAR 48x8-G-STEEL</p>	<p>GER001A TDS EARLY PPM60</p>
	<p>GER004 SPUR GEAR STEEL FITS ON BOSCH MOTOR 0130-821-324. Fits on> ELE133- Masats motor Revar Bosch motors</p>	<p>82534C92 Masats</p>
	<p>GER005 SPUR GEAR FITS IN GEAR BOX OF MASATS, REVAR & ISAF DOOR SYSTEM</p>	<p>GER005 TDS</p>

 <p>GER301</p>	<p>GER301 PULLEY 18T (EDRIVE GEARBOX)</p>	<p>GER301 TDS TREKABUS 16</p>
 <p>GER302</p>	<p>GER302 PULLEY 48T (EDRIVE GEARBOX)</p>	<p>GER302 TDS TREKABUS 16</p>
	<p>GER303-01 DRIVE PULLEY - SPD</p>	<p>H102187 Deans DEANS BELT GLIDER DOOR</p>
 <p>GER601</p>	<p>GER601 PULLEY BELT 174 (EDRIVE GEARBOX)</p>	<p>GER601 TDS TREKABUS 16</p>
 <p>GER603</p>	<p>GER603 DRIVE BELT GREEN - 3MTR</p>	<p>0105149 Deans DEANS BELT GLIDER DOOR</p>
 <p>GER606 20 x 3MTRS.</p>	<p>GER606 DRIVE BELT BLACK - 3MTR</p>	<p>0101111 Deans DEANS BELT PLUG SLIDER DOOR</p>
	<p>GER607 SET OF INTERNAL GEARS FOR EM06 GEARBOX</p>	<p>B603086 BCE</p>

	<p>LCK301 EMERGENCY RELEASE CABLE</p>	<p>LCK301 TDS TREKABUS 16</p>
	<p>LCK302-2000 CABLE INNER 2000x1.5 PEAR END LCK302-3000 CABLE INNER 3000x1.5 PEAR END</p>	<p>LCK302-2000 TDS LCK302-3000 TDS TREKABUS 16</p>
	<p>LCK303 CABLE OUTER AVAILABLE PER METRE</p>	<p>LCK303 TDS TREKABUS 16</p>
	<p>SPG002 TORSION SPRING 17mm leg</p>	<p>SPG002A TDS</p>
	<p>SPG003A STD COMPRESSION SPRING (EDRIVE SLIDE CLUTCH) HEAVY DUTY VERSION > BLACK = SPG005A</p>	<p>SPG003A TDS TREKABUS 16</p>
	<p>SPG004 CLOSE COILED TENSION SPRING 600mm x 9.6 o/d (TDS SENS EDGE)</p>	<p>SPG004 TDS OPTARE DOORS WITH SENS EDGE</p>

 <p>SPG007</p>	<p>SPG007 COMPRESSION SPRING (DOG CLUTCH)</p>	<p>214183 <i>Peters</i></p>
	<p>SPG008 DEANS SMALL 600mm SPRING</p>	<p>0104492 <i>Deans</i></p>
	<p>SPG010 FULL LOOPS EXTENSION SPRING</p>	<p>216023 <i>Peters</i> USED ON PETERS GLIDER DOOR LOCKS</p>
	<p>SPG011 COMPRESSION SPRING</p>	<p>216205 <i>Peters</i> USED ON PETERS GLIDER DOOR LOCKS</p>
	<p>SPG012 DEANS COMPRESSION SPRING</p>	<p>068004 <i>Deans</i></p>
	<p>SPG015 INNER CLUTCH SPRING</p>	<p>214642 <i>Peters</i></p>
 <p>SPG017</p>	<p>SPG017 DR FLAP RETURN SPRING NO.1 - DEANS</p>	<p>D49821 <i>Deans</i></p>

	<p>SPG018 DR FLAP RETURN SPRING NO.2 - DEANS</p>	<p>D49882 Deans</p>
	<p>SPG019 Id=14.75 Lg=25 swg=1.82 Top of doorshaft arm for Door height adjustment spring on Kirkert door system by Deans</p>	<p>0100604 Deans</p>
	<p>SPG020 SPRING CLIP (TDS FOLDER DOORS)</p>	<p>SPG020 TDS</p>
	<p>SPG021 INNER CLUTCH SPRING</p>	<p>0101248 Deans TRAVERSE CYLINDER – PLUG SLIDER</p>
	<p>SPG024 COMPRESSION SPRING</p>	<p>883143A0 Masats</p>
	<p>SPG025 COMPRESSION SPRING YELLOW</p>	<p>Tbc# Revar</p>
	<p>B704 CABLE PS 1225</p>	<p>B704 Ventura</p>

	<p>B705 CABLE PS 1485</p>	<p>B705 <i>Ventura</i></p>
	<p>C494 CATERPILLAR CABLE(L=500mm)</p>	<p>C494 <i>Ventura</i></p>
	<p>C495 CATERPILLAR CONNECTION</p>	<p>C495 <i>Ventura</i></p>
	<p>C714 TOOTHED BELT HTD36-3M-15</p>	<p>C714 <i>Ventura</i></p>
	<p>C715 TOOTHED BELT HTD 225-3M (75)</p>	<p>C715 <i>Ventura</i></p>
	<p>D172 CABLE 1314mm</p>	<p>D172 <i>Ventura</i> WRIGHTBUS STREETCAR PS</p>

	<p>D535 CABLE 1214mm</p>	<p>D535 <i>Ventura</i> ADL E200 SD PS + E400 DD PS, PLAXTON PRESIDENT DD PS, EAST LANCS SD PS + OLYMPUS DD PS, MCV SD EVOLUTION PS, POLISH SCANIA OMNICITY DD PS</p>
	<p>E324 SPRING - EMERGENCY CYLINDER</p>	<p>E324 <i>Ventura</i></p>
	<p>F164 PS CABLE 1410</p>	<p>F164 <i>Ventura</i></p>
	<p>J400 CABLE 1314mm ASSY</p>	<p>J400 <i>Ventura</i> WRIGHTBUS ECLIPSE SD PS + STREETCAR PS, OPTARE SD TEMPO PS</p>
	<p>J407 CABLE 1214mm ASSY</p>	<p>J407 <i>Ventura</i> OPTARE SD PS VERSA</p>
	<p>K745 FLAP TORSION SPRING</p>	<p>K745 <i>Ventura</i> IG3 ACTIVE FLAPS</p>

	<p>L794 FLAP TORSION SPRING (IG4 ACTIVE FLAPS)</p> <p>UPGRADED > SEE S555</p>	<p>L794 <i>Ventura</i> EARLIER IG4 ACTIVE FLAPS 2010-13</p>
	<p>O574 CABLE 1234mm ASSY</p>	<p>O574 <i>Ventura</i> WRIGHTBUS NBFL DD PS</p>
	<p>O575 CABLE PS 1234</p>	<p>O575 <i>Ventura</i></p>
	<p>S555 EXTENSION SPRING TR1310</p>  <p>< PREVIOUS VERSION</p>	<p>S555 <i>Ventura</i> IG4 ACTIVE FLAPS (2013 >)</p>
	<p>S929 PS Cable Assy (2xS951)</p>	<p>S929 <i>Ventura</i></p>
	<p>S951 PS2 CABLE 1579</p>	<p>S951 <i>Ventura</i></p>

	<p>VA0946 MOTOR SHAFT COUPLER 10-12</p>	<p>VA0946 <i>Ventura</i> ADL E200 EV PSE</p>
	<p>VA1035 PS2 CABLE 1425</p>	<p>VA1035 <i>Ventura</i></p>
	<p>VA1829 PS2 CABLE 1575 (NO EYELET)</p>	<p>VA1829 <i>Ventura</i></p>
	<p>VA6278 EMERGENCY CABLE ASSY (PEAR END) (USED WITH VA5470 DEVICE)</p>	<p>VA6278 <i>Ventura</i> MELLOR ORION RS ELEC MANUAL EMERG RELEASE</p>
	<p>VA7083 EMERGENCY CABLE ASSY (FORK END) (USED WITH VA7680 DEVICE)</p>	<p>VA7083 <i>Ventura</i> MELLOR ORION RS ELEC MANUAL EMERG RELEASE # LATEST</p>
	<p>VA8634 PS CABLE 1560MM</p>	<p>VA8946 <i>Ventura</i></p>